

Výtah z brožury

System spirál Optima

Embolizační spirály platinové pro léčbu intrakraniálních aneurysmat, řízeně elektro-termálně odpoutatelné pomocí tepelné spirály.

Design

Primární vinutí spirální, sekundární vinutí 3D (Complex) a 2D (Helical), systémy 10 a 18. Průměr sekundárního vinutí 1mm - 24mm, délka 1cm - 65cm. 3 tuhosti standard, soft a super soft.

Odpoutání do 1s pomocí jednotky XCEL. Světelné kontrolky pro odpoutání a stav baterie, použití max. pro 60 cyklů, sterilní balení.

Informace k objednání spirálek

Katalogové číslo	Popis - velikost
BALOPTI0101CSS10	Optima Coil Complex 10 Super Soft 1mm x 1cm
BALOPTI0102CSS10	Optima Coil Complex 10 Super Soft 1mm x 2cm
BALOPTI0103CSS10	Optima Coil Complex 10 Super Soft 1mm x 3cm
BALOPTI0104CSS10	Optima Coil Complex 10 Super Soft 1mm x 4cm
BALOPTI0152CSS10	Optima Coil Complex 10 Super Soft 1.5mm x 2cm
BALOPTI0153CSS10	Optima Coil Complex 10 Super Soft 1.5mm x 3cm
BALOPTI0154CSS10	Optima Coil Complex 10 Super Soft 1.5mm x 4cm
BALOPTI0202CSS10	Optima Coil Complex 10 Super Soft 2mm x 2cm
BALOPTI0203CSS10	Optima Coil Complex 10 Super Soft 2mm x 3cm
BALOPTI0204CSS10	Optima Coil Complex 10 Super Soft 2mm x 4cm
BALOPTI0206CSS10	Optima Coil Complex 10 Super Soft 2mm x 6cm
BALOPTI0208CSS10	Optima Coil Complex 10 Super Soft 2mm x 8cm
BALOPTI0253CSS10	Optima Coil Complex 10 Super Soft 2.5mm x 3cm
BALOPTI0254CSS10	Optima Coil Complex 10 Super Soft 2.5mm x 4cm
BALOPTI0256CSS10	Optima Coil Complex 10 Super Soft 2.5mm x 6cm
BALOPTI0304CSS10	Optima Coil Complex 10 Super Soft 3mm x 4cm
BALOPTI0306CSS10	Optima Coil Complex 10 Super Soft 3mm x 6cm
BALOPTI0308CSS10	Optima Coil Complex 10 Super Soft 3mm x 8cm
BALOPTI0310CSS10	Optima Coil Complex 10 Super Soft 3mm x 10cm

Katalogové číslo	Popis - velikost
BALOPTI0356CSS10	Optima Coil Complex 10 Super Soft 3.5mm x 6cm
BALOPTI0358CSS10	Optima Coil Complex 10 Super Soft 3.5mm x 8cm
BALOPTI0406CSS10	Optima Coil Complex 10 Super Soft 4mm x 6cm
BALOPTI0408CSS10	Optima Coil Complex 10 Super Soft 4mm x 8cm
BALOPTI0410CSS10	Optima Coil Complex 10 Super Soft 4mm x 10cm
BALOPTI0508CSS10	Optima Coil Complex 10 Super Soft 5mm x 8cm
BALOPTI0510CSS10	Optima Coil Complex 10 Super Soft 5mm x 10cm
BALOPTI0513CSS10	Optima Coil Complex 10 Super Soft 5mm x 13cm
BALOPTI0203CSF10	Optima Coil Complex 10 Soft 2mm x 3cm
BALOPTI0204CSF10	Optima Coil Complex 10 Soft 2mm x 4cm
BALOPTI0206CSF10	Optima Coil Complex 10 Soft 2mm x 6cm
BALOPTI0208CSF10	Optima Coil Complex 10 Soft 2mm x 8cm
BALOPTI0255CSF10	Optima Coil Complex 10 Soft 2.5mm x 5cm
BALOPTI0306CSF10	Optima Coil Complex 10 Soft 3mm x 6cm
BALOPTI0308CSF10	Optima Coil Complex 10 Soft 3mm x 8cm
BALOPTI0310CSF10	Optima Coil Complex 10 Soft 3mm x 10cm
BALOPTI0407CSF10	Optima Coil Complex 10 Soft 4mm x 7cm
BALOPTI0413CSF10	Optima Coil Complex 10 Soft 4mm x 13cm
BALOPTI0509CSF10	Optima Coil Complex 10 Soft 5mm x 9cm
BALOPTI0517CSF10	Optima Coil Complex 10 Soft 5mm x 17cm
BALOPTI0611CSF10	Optima Coil Complex 10 Soft 6mm x 11cm
BALOPTI0620CSF10	Optima Coil Complex 10 Soft 6mm x 20cm
BALOPTI0713CSF10	Optima Coil Complex 10 Soft 7mm x 13cm
BALOPTI0724CSF10	Optima Coil Complex 10 Soft 7mm x 24cm
BALOPTI0816CSF10	Optima Coil Complex 10 Soft 8mm x 16cm
BALOPTI0827CSF10	Optima Coil Complex 10 Soft 8mm x 27cm
BALOPTI0517CST10	Optima Coil Complex 10 Standard 5mm x 17cm
BALOPTI0611CST10	Optima Coil Complex 10 Standard 6mm x 11cm
BALOPTI0620CST10	Optima Coil Complex 10 Standard 6mm x 20cm
BALOPTI0713CST10	Optima Coil Complex 10 Standard 7mm x 13cm
BALOPTI0724CST10	Optima Coil Complex 10 Standard 7mm x 24cm
BALOPTI0816CST10	Optima Coil Complex 10 Standard 8mm x 16cm
BALOPTI0827CST10	Optima Coil Complex 10 Standard 8mm x 27cm
BALOPTI0923CST10	Optima Coil Complex 10 Standard 9mm x 23cm
BALOPTI0930CST10	Optima Coil Complex 10 Standard 9mm x 30cm
BALOPTI1027CST10	Optima Coil Complex 10 Standard 10mm x 27cm
BALOPTI1034CST10	Optima Coil Complex 10 Standard 10mm x 34cm
BALOPTI0620COM18	Optima Coil Complex 18 6mm x 20cm
BALOPTI0724COM18	Optima Coil Complex 18 7mm x 24cm
BALOPTI0827COM18	Optima Coil Complex 18 8mm x 27cm
BALOPTI0930COM18	Optima Coil Complex 18 9mm x 30cm

Katalogové číslo	Popis - velikost
BALOPTI1034COM18	Optima Coil Complex 18 10mm x 34cm
BALOPTI1137COM18	Optima Coil Complex 18 11mm x 37cm
BALOPTI1240COM18	Optima Coil Complex 18 12mm x 40cm
BALOPTI1343COM18	Optima Coil Complex 18 13mm x 43cm
BALOPTI1447COM18	Optima Coil Complex 18 14mm x 47cm
BALOPTI1550COM18	Optima Coil Complex 18 15mm x 50cm
BALOPTI1655COM18	Optima Coil Complex 18 16mm x 55cm
BALOPTI1860COM18	Optima Coil Complex 18 18mm x 60cm
BALOPTI2065COM18	Optima Coil Complex 18 20mm x 65cm
BALOPTI2265COM18	Optima Coil Complex 18 22mm x 65cm
BALOPTI2465COM18	Optima Coil Complex 18 24mm x 65cm
BALOPTI0101HSS10	Optima Coil Helical 10 Super Soft 1mm x 1cm
BALOPTI0102HSS10	Optima Coil Helical 10 Super Soft 1mm x 2cm
BALOPTI0103HSS10	Optima Coil Helical 10 Super Soft 1mm x 3cm
BALOPTI0104HSS10	Optima Coil Helical 10 Super Soft 1mm x 4cm
BALOPTI0151HSS10	Optima Coil Helical 10 Super Soft 1.5mm x 1cm
BALOPTI0152HSS10	Optima Coil Helical 10 Super Soft 1.5mm x 2cm
BALOPTI0153HSS10	Optima Coil Helical 10 Super Soft 1.5mm x 3cm
BALOPTI0154HSS10	Optima Coil Helical 10 Super Soft 1.5mm x 4cm
BALOPTI0201HSS10	Optima Coil Helical 10 Super Soft 2mm x 1cm
BALOPTI0202HSS10	Optima Coil Helical 10 Super Soft 2mm x 2cm
BALOPTI0203HSS10	Optima Coil Helical 10 Super Soft 2mm x 3cm
BALOPTI0204HSS10	Optima Coil Helical 10 Super Soft 2mm x 4cm
BALOPTI0206HSS10	Optima Coil Helical 10 Super Soft 2mm x 6cm
BALOPTI0208HSS10	Optima Coil Helical 10 Super Soft 2mm x 8cm
BALOPTI0253HSS10	Optima Coil Helical 10 Super Soft 2.5mm x 3cm
BALOPTI0254HSS10	Optima Coil Helical 10 Super Soft 2.5mm x 4cm
BALOPTI0256HSS10	Optima Coil Helical 10 Super Soft 2.5mm x 6cm
BALOPTI0304HSS10	Optima Coil Helical 10 Super Soft 3mm x 4cm
BALOPTI0306HSS10	Optima Coil Helical 10 Super Soft 3mm x 6cm
BALOPTI0308HSS10	Optima Coil Helical 10 Super Soft 3mm x 8cm
BALOPTI0310HSS10	Optima Coil Helical 10 Super Soft 3mm x 10cm
BALOPTI0406HSS10	Optima Coil Helical 10 Super Soft 4mm x 6cm
BALOPTI0408HSS10	Optima Coil Helical 10 Super Soft 4mm x 8cm
BALOPTI0410HSS10	Optima Coil Helical 10 Super Soft 4mm x 10cm
BALOPTI0506HSS10	Optima Coil Helical 10 Super Soft 5mm x 6cm
BALOPTI0508HSS10	Optima Coil Helical 10 Super Soft 5mm x 8cm
BALOPTI0510HSS10	Optima Coil Helical 10 Super Soft 5mm x 10cm
BALOPTI0615HST10	Optima Coil Helical 10 Standard 6mm x 15cm
BALOPTI0620HST10	Optima Coil Helical 10 Standard 6mm x 20cm
BALOPTI0720HST10	Optima Coil Helical 10 Standard 7mm x 20cm
BALOPTI0730HST10	Optima Coil Helical 10 Standard 7mm x 30cm
BALOPTI0820HST10	Optima Coil Helical 10 Standard 8mm x 20cm

Katalogové číslo	Popis - velikost
BALOPTI0930HST10	Optima Coil Helical 10 Standard 9mm x 30cm
BALOPTI1030HST10	Optima Coil Helical 10 Standard 10mm x 30cm
BALOPTI0304HSF10	Optima Coil Helical 10 Soft 3mm x 4cm
BALOPTI0306HSF10	Optima Coil Helical 10 Soft 3mm x 6cm
BALOPTI0308HSF10	Optima Coil Helical 10 Soft 3mm x 8cm
BALOPTI0310HSF10	Optima Coil Helical 10 Soft 3mm x 10cm
BALOPTI0406HSF10	Optima Coil Helical 10 Soft 4mm x 6cm
BALOPTI0408HSF10	Optima Coil Helical 10 Soft 4mm x 8cm
BALOPTI0410HSF10	Optima Coil Helical 10 Soft 4mm x 10cm
BALOPTI0506HSF10	Optima Coil Helical 10 Soft 5mm x 6cm
BALOPTI0508HSF10	Optima Coil Helical 10 Soft 5mm x 8cm
BALOPTI0510HSF10	Optima Coil Helical 10 Soft 5mm x 10cm
BALOPTI0606HSF10	Optima Coil Helical 10 Soft 6mm x 6cm
BALOPTI0608HSF10	Optima Coil Helical 10 Soft 6mm x 8cm
BALOPTI0610HSF10	Optima Coil Helical 10 Soft 6mm x 10cm
BALXCEL	Xcel Controller